


Preliminary
Specifications Subject to Change without notice.



PIXCI® SI1
Frame Grabber

Available
Soon

PIXCI® SI2
Frame Grabber



PIXCI® SI4
Frame Grabber



SV643 Camera High Frame Rate Camera
(Lens Optional)

| | |
|------------------------|---|
| Optical Format: | 1/2-inch |
| Active Image Size: | 6.3mm(H) x 4.7mm(V) 7.8mm Diagonal |
| Active Pixels: | 640H x 480V |
| Pixel Size: | 9.9µm x 9.9µm |
| Color Filter Array: | Monochrome or Color RGB Bayer Pattern |
| Shutter Type: | Electronic Snapshot (Global) Shutter |
| Maximum Data Rate: | 70 MPS |
| Master Clock: | 70 MHz |
| Frame Rate: | 211 fps (at full resolution) |
| ADC Resolution: | 10-bit, on-chip |
| Responsivity: | 17 Volts/Lux-sec |
| Dynamic Range: | 61dB linear |
| Supply Voltage: | 5 to 12 Volts |
| Power Consumption: | 190 mWatt |
| Operating Temperature: | -40°C to +70°C |
| Camera Dimensions: | 1.89" L x 1.49" H x 0.83" D 48mm L x 38mm H x 21mm D |
| Weight: | 1.4 oz / 39 grams |


High Speed & Low Cost Silicon Video® 643

The **SILICON VIDEO®** monochrome **643M** and color **643C** cameras provide 640 by 480 resolution at 211frames per second (fps). Reducing the number of lines to 2 allows frame rates up to 26,636 fps. Fast frame rates, global shutter, asynchronous reset, and shutter speeds as short as 1 microsecond (1/1,000,000th of a second) provide sharp images of high-speed motion. Example applications include high-speed inspection, particle tracking, kinematics, collision studies, sports analysis, ballistics, and plant or animal motion analysis. Images can be captured at rates above 200 frames per second and can then be played-back at slow display rates to reveal previously undetected details. Individual frames can be extracted from a sequence for further analysis or measurement.

The rugged aluminum camera case is 48 mm high by 38 mm wide by 21 mm deep. Each side of the case has two M2-0.4 screw holes for attaching the ¼-20 tripod adapter or for mounting. The flexible, category 5e, shielded RJ-45 interface cable provides image data transfer, camera control, and camera power while allowing camera positioning in tight spaces. Optional cables with right angle connectors and thumbscrews are available.

This progressive scan camera connects to the PCI Express bus thru the PIXCI® SI1 (one camera), PIXCI® SI2 (two camera), or PIXCI® SI4 (four camera) imaging board. In addition to providing power, camera control, and data transfer, the PIXCI® SI boards have a trigger input and a strobe output to synchronize external equipment.

Also available is the SV643 camera with an EPIX® imaging computer system that can be configured to capture for a specified frame rate and time period. The SILICON VIDEO® 643 camera is available from EPIX, Inc., or from an authorized EPIX, Inc. Distributor.



פד"מ-טק (1991) בע"מ
 מייקל סטורץ | 02.583.2511
 PaZaM-tech@pobox.com
 www.PaZaM-tech.co.il

SV643 High Speed Digital Cameras

CAMERA CONTROL SOFTWARE

Sequence Capture with SV643 Camera and XCAP Imaging Program

The SILICON VIDEO® 643 camera is designed to capture thousands of images at fast frame rates.

XCAP-Lite will capture for a maximum of one second at full resolution, 8 bits per pixel, and maximum frame rate. images must be saved individually.


The XCAP-LTD program captures and saves sequences for more than 2 minutes into 8 GBytes of available memory (computer must have approximately 10 GBytes of installed memory).

The XCAP-STD imaging program

offers video to disk, which allows sequences of images to be captured directly to as few as two hard disks configured as RAID 0. Using four 500 GB hard drives, 7200 rpm, images can be captured continuously for 8 hours (640 x 480 resolution, 8-bits per pixel, 211 fps). Longer durations are possible.

The XCAP program is optimized for capturing image sequences. The **Capture Rate & Mode** window allows selection of sequence length and interval rate.

Linear and Circular sequences are offered. A **Linear Sequence** is a simple capture of a preset number of frames. A **Circular Sequence** offers continuous capture until an event stop. The **Capture Event** window offers different conditions that can start, modulate, or stop sequence capture. Events include (among




XCAP Capture Rate & Mode

others) *Date & Time, RS-232 Signal, or a Mouse Click.*

Images can be overlaid with frame number and time stamp. XCAP offers 16 different time stamp formats.

The **Display Rate** window provides automatic playback at rates easily selected by the user. A sequence can be displayed once, or can be displayed continuously. Display can progress from beginning to end or in reverse. A subset of frames, extracted from the complete sequence, can be displayed or saved.

XCAP compliments the SV642 camera with sequence capture, display, processing, analyzing, and saving operations. Select which version of the XCAP program is best for your application by reviewing the description at <http://www.epixinc.com/products/xcap.htm>.



XCAP Capture Event

SV643C & SV643M High Frame Rate Color/Mono Cameras

| Frame Resolution | Pixel Clock Frequency | | | |
|------------------|-----------------------|------------|------------|------------|
| | 25 MHz | 48 MHz | 66 MHz | 70 MHz |
| 640 x 480 | 75 fps | 145 fps | 199 fps | 211 fps |
| 512 x 480 | 93 fps | 178 fps | 245 fps | 260 fps |
| 480 x 360 | 138 fps | 260 fps | 358 fps | 380 fps |
| 320 x 240 | 303 fps | 568 fps | 781 fps | 828 fps |
| 240 x 180 | 527 fps | 976 fps | 1,343 fps | 1,424 fps |
| 8 x 480 | 953 fps | 1,831 fps | 2,517 fps | 2,670 fps |
| 120 x 90 | 1,911 fps | 3,406 fps | 4,683 fps | 4,967 fps |
| 64 x 46 | 5,835 fps | 9,700 fps | 13,338 fps | 14,147 fps |
| 640 x 2 | 10,794 fps | 18,264 fps | 25,114 fps | 26,636 fps |

Note: Cable length tests specific to the SV643 camera have yet to be conducted. Contact EPIX, Inc., technical support if a cable length greater than 14 feet will be used. Cable lengths greater than 14 feet (4.2 meters) may require use of a pixel clock frequency less than 70 MHz -- which, as indicated in the SV643 frame rate chart, will result in reduced frame rates.



EPIX, Incorporated
381 Lexington Drive
Buffalo Grove, IL 60089 USA
Tel - 847 465 1818
Fax - 847 465 1919
epix@epixinc.com
E-mail: sales@epixinc.com

Specifications subject to change without notice. EPIX and PIXCI are registered trademarks of EPIX, Inc. XCAP is a trademark of EPIX, Inc. EPIX® imaging products are made in the USA. © 2009 EPIX, Inc. All Rights Reserved. 6 NOV 2009